Issue no.: 20**-00***
Lot.CE
Issue date: m** d**, y20**

KANSO TECHNOS CO., LTD.



Certificate of Analysis



Certified Reference Material KANSO CRM Lot.CE

Reference Material for Nutrients in Seawater (RMNS)

This certified reference material (CRM) was produced using treated natural seawater on the basis of quality control system under ISO 17034 (JIS Q 17034), for use in managing analysis precision or verifying performance of analytical methods or instruments for analysis of nutrients in seawater or matrices similar to seawater.

1. Name and Location of the Manufacturer/Analysis Facility

KANSO TECHNOS CO., LTD.

Laboratory for Instrumentation and Analysis

3-1-1, Higashikuraji, Katano, Osaka, 576-0061, Japan

2. Name of Reference Material and Sample Form

Name: Reference Material for Nutrients in Seawater (RMNS)

Sample: About 90 mL of this CRM solution in a 100 mL polypropylene bottle (vacuum-sealed in aluminum-film bag).

3. Certified Values

The certified values of 4 types of nutrients are shown in the table below. The expanded uncertainty in the table represents combined standard uncertainty calculated using a coverage factor of 2 which gives approximately 95 % level of confidence. The standard deviation (SD) of between-bottle is calculated based on the results of 150 bottles measured in duplicates (except for nitrite: 20 bottles measured for recertification), following ISO Guide 35 (JIS Q 0035) guideline.

Issue no.: 20**-00***
Lot.CE Issue date: m** d**, y20**

	Certified	Expanded	Between-		
	Value	Value Uncertainty Bottle SD		Analysis Method	
	(µmol/kg)	(µmol/kg)	(µmol/kg)		
Nitrate	0.01*	0.03	0.003	Japan Meteorological Agency,	
				Manual for Oceanographic Observation (1999);	
				Cu-Cd reduction Naphthylethylenediamine	
				photometric method (section 5.5.7.3)	
Nitrite	0.03**	0.03	0.0010	Japan Meteorological Agency,	
				Manual for Oceanographic Observation (1999);	
				Naphthylethylenediamine photometric method	
				(section 5.5.7.4)	
				Japan Meteorological Agency,	
Silicate	0.06*	0.09	0.009	Manual for Oceanographic Observation (1999);	
				Molybdenum blue method (section 5.5.7.2)	
Phosphate	0.012*	0.006	0.0007	Japan Meteorological Agency,	
				Manual for Oceanographic Observation (1999);	
				Molybdenum blue method (section 5.5.7.1)	

^{*} The values for nitrate, silicate, and phosphate are below quantifiable detection limit (QDL), thus use these values as a guide.

4. Value Determination

The certified values were arithmetic means of the results of 30 bottles each measured in duplicates (except for nitrite: 10 bottles each) analyzed by KANSO TECHNOS CO., LTD. (KANSO) and Japan Agency for Marine-Earth Science and Technology (JAMSTEC) with colorimetric method (continuous flow analysis, CFA, method). The salinity of calibration solutions was adjusted to the salinity of this $CRM \pm 0.5$ psu.

5. Traceability

Each certified value of nitrate, nitrite, and phosphate was determined by one of Japan Calibration Service System (JCSS) standard solutions for each nitrate ions, nitrite ions, and phosphate ions. Silicate value was determined by one of Merck KGaA silicon standard solution 1000 mg/L Si traceable to National Institute of Standards and Technology (NIST) silicon standard reference material (SRM) 3150. Along with the measurement of this CRM, the National Metrology Institute of Japan (NMIJ) CRMs (Seawater for Nutrients) and KANSO CRMs were analyzed. The results of the measured CRMs uncertainty ranges and expanded uncertainty (k = 2) of the certified values overlapped one another. The tables below describe the standard lots and CRMs used during the analysis.

Standard solutions lot number.

	Supplier	Name / Description	Lot Number
Nitrate	FUJIFILM Wako Pure Chemical Corporation	Nitrate Ion Standard Solution (NO ₃ ⁻ 1000)	KPM0510
Nitrite	FUJIFILM Wako Pure Chemical Corporation	Nitrite Ion Standard Solution (NO ₂ -1000)	ESQ6029
Silicate	Merck KGaA	Silicon Standard Solution (Si 1000 mg/L)	HC41358736
Phosphate	FUJIFILM Wako Pure Chemical Corporation	Phosphate Ion Standard Solution (PO ₄ ³⁻ 1000)	KPF6893

^{**} The value for nitrite was recertified on 2021/1/25. Concerning RMNS nitrite, a trend of increasing concentration (0.004±0.002 μmol/kg per year) has been confirmed.

Issue no.: 20**-00***
Lot.CE
Issue date: m** d**, y20**

CRMs measured during this certification analysis.

	<u> </u>
	NMIJ CRM Number / Lot Number
NMIJ CRMs	7601-a, 7602-a, 7603-a
KANSO CRMs	BY, BU, CD, CA, BW, CC ,BV, CB, BZ
(for nitrite recertification)	7602-a, CI, CO, CG

*

6. Raw Material and Processing Method

Collected location: Eastern Gyre of the Mediterranean Sea (38 $^{\circ}$ N, 16 $^{\circ}$ E); surface seawater. Raw seawater was filtered (0.45 μ m membrane filter), autoclave treatments (2 sets of 120 $^{\circ}$ C for 2 h) conducted, and about 90 mL aliquots of treated seawater were transferred into 100 mL polypropylene bottles in a clean room. (No additives)

7. Intended Use

Seawater nutrient reference material solution for nutrients analysis. (Do not use for other purposes)

8. Storage and Usage Specifications

Do not freeze (the composition of the product may change).

Store at room temperature below 40 °C.

Because of no additives or preservatives, the quality is not ensured for reuse after opening the outer seal.

Do not dilute or concentrate the product.

Shake well and open the seal right before use.

When sampling the product, do not insert objects to prevent contamination.

9. Certified Date

2016/11/17

10. Production Date

2015/10/29

1 1. Expiration and Guarantee Date

Under unopened and stored condition described in section 8, this CRM's expiration and guarantee date is 2022/10/28

12. Homogeneity

Out of 2500 bottles produced, 5 sets, each set consisting of randomly selected 30 bottles were analyzed (total of 150 bottles analyzed). For nitrite recertification, 2 sets, consisting of randomly selected 10 bottles were analyzed (total of 20 bottles analyzed). The level of homogeneity was assessed from the results and confirmed acceptable homogeneity. Uncertainty associated with sample homogeneity is reflected in the uncertainties of the certified values. The standard deviations of between-bottle for the bottles analyzed are given in the table in section 3.

Issue no.: 20**-00***
Lot.CE Issue date: m** d**, y20**

13. Additional Information

(1) Salinity **35.224 psu** (standard deviation 0.0004 psu; n = 10)

An electrical conductivity measurement method in Japan Meteorological Agency's Manual for Oceanographic Observation (1999) was used to measure salinity.

(2) RMNS nitrite

An increasing trend $(0.004 \pm 0.002 \, \mu \text{mol/kg per year})$ has been confirmed.

14. Health and Safety

Do not eat or drink the product.

Because the product is seawater, generally, it can be disposed by diluting; however, follow local jurisdictions when carrying out the disposal procedure.

15. Limitations of Copied Certificate

When copying this certificate, make clear indication as such in the copied certificate.

16. Technical Information

The buyer of this CRM shall be notified when changes in property values and/or any important changes are made in relation to this product. For more technical information, contact us at the address or webpage below.

17. Name and Signature of Party Responsible for Production and Certification

KANSO TECHNOS CO., LTD.

Laboratory for Instrumentation and Analysis

Director: Takashi KITAO

Revision history

2021/07/01; The company name and logo were changed to a new version.

2021/1/25; The property value for nitrite was recertified.

2020/11/02; ILAC MRA symbol was added to the certificate.

2020/07/01; The company logo was changed to a new version.

2020/4/3; The IAJapan accreditation symbol was changed due to the revision of ISO/IEC/17011

(JIS Q 17011)

2020/4/3; The lot numbers of the standard solutions were added.

2020/4/3; The lot numbers of the certified reference materials measured with the certification analysis

were added.

For any inquiry, please contact us



KANSO TECHNOS CO., LTD.

Laboratory for Instrumentation and Analysis 3-1-1, Higashikuraji, Katano, Osaka, 576-0061, Japan

TEL: +81-72-810-6551 FAX: +81-72-810-6552

E-mail: RMinfo@kanso.co.jp

Webpage: http://www.kanso.co.jp/eng/production/index.html